




LEFT SIDE VIEW
SIDE COVER SHOWN



FRONT VIEW
DOOR SHOWN



FRONT VIEW
DOOR REMOVED



RIGHT SIDE VIEW
NO SIDE COVER

This Document Contains Proprietary and Confidential Information.
Duplication, reproduction or use of this document or its contents in any form other than as expressly permitted by Kinney Electrical Mfg. Co., is prohibited.

MITSUBISHI ELECTRIC POWER PRODUCTS, INC.
WARRENDALE, PA

REVISIONS

PART NO. **SIDECAR 12A**

DESCRIPTION **SIDECAR CABINET 9900A, 80-225KVA**

MEPPI APPROVED

KINNEY APPROVED

REVISION *

DATE **05-07-09**

CAD FILE

DRAWING NO.


SHEET

DRAWN BY **GM / RH**

SCC99002251202

M0000394

1 OF 2



PLAN VIEW
ANCHOR DETAIL

BUS TERMINAL DETAIL

SIDECAR NOTES:

SERIES: 9900A

KVA: 80-225

ENCLOSURE: NEMA 1 (UL 50 LISTED ENCLOSURE).

BOX: 12 GAUGE PAINTED STEEL, CONTINUOUSLY WELDED SEAMS AND CORNERS. EQUIPPED WITH REMOVABLE ALUMINUM TOP COVER, NO KNOCKOUTS.

DOOR: 12 GAUGE PAINTED STEEL EQUIPPED WITH MITSUBISHI HANDLE WITH THREE POINT CATCH.

FINISH: MITSUBISHI BEIGE POLYESTER POWDERCOAT APPLIED TO SURFACES TREATED WITH AN IRON PHOSPHATE AND CHROME FREE SEALER.

BUS BAR: 800AMP, ELECTROLYTIC COPPER OF 98% CONDUCTIVITY, BASED ON 1000AMPS PER SQUARE INCH DENSITY, SILVER PLATED.

TERMINAL LUGS: (4) #4-600MCM LUGS PER TERMINATION.

This Document Contains Proprietary and Confidential Information.
Duplication, reproduction or use of this document or its contents in any form other than as expressly permitted by Kinney Electrical Mfg. Co., is prohibited.

MITSUBISHI ELECTRIC POWER PRODUCTS, INC.
WARRENDALE, PA

REVISIONS				PART NO. SIDE CAR 12A	
				DESCRIPTION SIDE CAR CABINET 9900A, 80-225KVA	
			MEPPI APPROVED	KINNEY APPROVED	REVISION *
			DATE 05-07-09	CAD FILE	DRAWING NO. SHEET
			DRAWN BY GM / RH	SCC99002251202	M0000394 2 OF 2