
# 9900D DATA SHEET 1200, 1250, 1500, 1600, 2000 kVA





## HIGH EFFICIENCY %



#### **AC/AC EFFICIENCY CURVES**

Load %	1200/1250 kVA	1500/1600 kVA	2000 kVA
25%	96.0%	96.3%	96.3%
50%	97.0%	96.9%	97.0%
75%	97.0%	97.0%	97.0%
100%	96.8%	96.9%	96.9%

## FEATURES & BENEFITS WHAT



1	S	oace	saving	footpri	n

True on-line double conversion

Up to 97% efficient

Modularity allows for N or N+1 reliability

Expandable in 400kVA increments

Load bank free burn-in test capability

Rated Output	1200 kVA (1200 kW)	1250 kVA (1250 kW)	1500 kVA (1500 kW)	1600 kVA (1600 kW)	2000 kVA (2000 kW)		
AC INPUT							
Configuration	3 phase, 3 wire						
Voltage	480V +15%, -20%						
Frequency	60 Hz ±10%						
Power Factor	> 0.98 lagging						
Reflected Current THD	3% typ. at 100% load; 6% typ. at 50% load						
BATTERY							
Nominal Voltage	480 Vdc						
Minimum Voltage	400 Vdc						
Float Voltage	Up to 600 Vdc						
Туре	VRLA, VLA, NiCad, Lithium Ion						
AC OUTPUT							
Configuration	3 phase, 3 wire						
Voltage	480V						
Voltage Regulation	±1% for balanced load; 2% at 100% for unbalanced load						
Voltage Balance	2%						
Voltage THD	<2% at 100% linear load; <5% at 100% non-linear load						
Transient Response	±5% for step load; ±1% for loss/return of AC input; ±5% for retransfer from bypass to inverter						
Transient Recovery Time	20 ms						
Frequency	60 Hz						
Frequency Regulation	±0.01% in free running mode						
Phase Displacement	±1° for 100% balanced load; 3° for 100% unbalanced load						
Power Factor	1.0						
Overload Capacity	105%-110% for 60 min; 111%-125% for 10 min; 126%-150% for 1 min						
ENVIRONMENTAL							
Cooling	Forced Air						
Operating Temperature	32°F to 104°F (0°C to 40°C)						
Relative Humidity	5% to 95% non-condensing; recommended 30% to 90%						
Altitude	0 to 6500 feet no derating (1981 m)						
Location	Temperature-controlled, indoor area free of conductive contaminants						
Clearance Required (Max)	Top: 23.6 in; Front: 39.4 in; Rear: 0 in						
GENERAL							
Weight	7270 lb (3300 kg)	7270 lb (3300 kg)	9750 lb (4423 kg)	9750 lb (4423 kg)	11470 lb (5220 kg)		

## **ABOUT US**

Based in Pittsburgh, PA, the Critical Power Solutions Division (CPSD) is a business unit of Mitsubishi Electric Power Products, Inc. (MEPPI). Mitsubishi Electric has been manufacturing precision engineered highly reliable uninterruptible power supplies since 1964 and introduced a line of cooling systems in 2021. CPSD's operations include Project Application Engineering, Design Engineering, Service & Support, Manufacturing & Warehousing, Quality, Sales and Marketing.



Dimensions (WxDxH) (In) Heat Rejection

(kBTU/Hr) @ 100% Load

### **OUR SERVICES**

133.9 x 35.4 x 80.7

135.4

Mitsubishi Electric's highly reliable and efficient products are backed by a full range of Field and Factory Services:

133.9 x 35.4 x 80.7

141.0





Batteries & Battery Services







169.3 x 35.4 x 80.7 169.3 x 35.4 x 80.7

174.6

163.7



192.9 x 35.4 x 80.7

218.3





